



# CERTIFICATE OF PRODUCT CERTIFICATION

**CERTIFICATE NO.:** CQC17010166236

**Valid from:** Jan.11,2023

**Valid until:** Nov.01,2027

**NAME AND REGISTERED ADDRESS OF THE APPLICANT** Rittal GmbH & Co. KG  
Auf dem Stützelberg, D-35745 Herborn, Germany

**NAME AND REGISTERED ADDRESS OF THE MANUFACTURER** STEINEL GmbH  
Dieselstrasse 80-84, 33442 Herzebrock-Clarholz, Germany

**NAME AND LOCATION OF THE FACTORY** STEINEL Electronic S.R.L.  
Str. Ramnicu Valcea Nr. 79-115300 Curtea de Arges, Romania

**PRODUCT NAME, MODEL AND SPECIFICATION** Fixed Luminaire For LED Modules (Ceiling Mounted / Wall Mounted, A.C. Supplied Electronic Controlgear For LED Modules, Class III, IP20, Suitable For Direct Mounting On Normally Flammable Material, ta:55°C)  
SZ 2500.220 11W (24×0.36W/LED Module) 24DC 420mA. The maximum number of luminaires for looping-in connection is 15.

**THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS** GB/T 17743-2021;GB 7000.1-2015;GB 7000.201-2008

**TYPE OF CERTIFICATION SCHEMES** Type Testing of Product + Initial Factory Inspection + Follow up Factory Inspection

This is to certify that the above mentioned product(s) complies with the requirements of certification rules of CQC11-465314-2016.

Date of original issued: Apr.10,2017

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

The certificate information is available through the QR code below or CNCA's website: [www.cnca.gov.cn](http://www.cnca.gov.cn)



SIGNATURE:

谢肇煦



CHINA QUALITY CERTIFICATION CENTRE



# 产品认证证书

证书编号: CQC17010166236

发证日期: 2023年01月11日

有效期至: 2027年11月01日

**委托人名称** Rittal GmbH & Co. KG  
**及注册地址** Auf dem Stützelberg, D-35745 Herborn, 德国

**制造商名称** STEINEL GmbH  
**及注册地址** Dieselstrasse 80-84, 33442 Herzebrock-Clarholz, 德国

**生产企业名称** STEINEL Electronic S.R.L.  
**及生产地址** Str. Ramnicu Valcea Nr. 79-115300 Curtea de Arges, 罗马尼亚

**产品名称和系列、规格、型号** 固定式灯具 (LED 灯具, 吸顶式/壁式, LED 模块用交流电子控制装置, III类, IP20, 适宜直接安装在普通可燃材料表面, ta:55°C)  
SZ 2500.220 11W (24×0.36W/LED Module)。24VDC 420mA, 灯具可用于环路连接, 连接灯具的最大数量为 15 支。

**产品标准和技术要求** GB/T 17743-2021;GB 7000.1-2015;GB 7000.201-2008

**认证模式** 产品型式试验+初次工厂检查+获证后监督

上述产品符合 CQC11-465314-2016 认证规则的要求, 特发此证。  
本证书为变更证书, 证书首次颁发日期: 2017年04月10日  
证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

可通过扫描下方二维码或登录国家认监委网站 ( www.cnca.gov.cn ) 查验证书信息



签发: 谢肇煦



中国质量认证中心