



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

CERTIFICATE NO.: 2016011001924336

Valid from: Jan.11,2023

Valid until: Nov.01,2027

NAME AND REGISTERED ADDRESS OF THE APPLICANT Rittal GmbH & Co. KG
Auf dem Stützelberg, D-35745 Herborn, Germany

NAME AND REGISTERED ADDRESS OF THE MANUFACTURER STEINEL GmbH
Dieselstrasse 80-84, 33442 Herzebrock-Clarholz, Germany

NAME AND LOCATION OF THE FACTORY STEINEL Electronic S.R.L.
Str. Ramnicu Valcea Nr. 79-115300 Curtea de Arges, Romania

PRODUCT MODEL(S) Fixed Luminaire For LED Modules (Ceiling Mounted / Wall Mounted, A.C. Supplied Electronic Controlgear For LED Modules, Class II, IP20, Suitable For Direct Mounting On Normally Flammable Material, ta:55°C)
See Appendix : 100-230V ~ 50/60Hz

STANDARDS AND TECHNICAL REQUIREMENTS GB/T 17743-2021;GB 7000.1-2015;GB 7000.201-2008

This is to certify that the above mentioned product(s) complies with the requirements of implementation rules for compulsory certification(REFNO. CNCA-C10-01:2014)

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

Date of original issued: Dec.01,2016

Accredited by China National Accreditation Service for Conformity Assessment CNAS C001-P

The certificate information is available through the QR code below or CNCA's website: www.cnca.gov.cn



SIGNATURE:

谢肇煦



CHINA QUALITY CERTIFICATION CENTRE



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

CERTIFICATE NO. : 2016011001924336

page 1 of 1

paper:

This certificate and attachments shall be used at the same time, and the verification instructions can be found in the main certificate.

型号	额定功率	光源功率	感应器	环路最多安装样品数量(个)	插座
SZ 2500.310	13W	32× 0.36W/LED	有	10	有
SZ 2500.311	13W	32× 0.36W/LED	有	10	有
SZ 2500.312	13W	32× 0.36W/LED	有	10	有
SZ 2500.313	13W	32× 0.36W/LED	有	10	有
SZ 2500.300	13W	32× 0.36W/LED	有	15	无
SZ 2500.200	11W	24× 0.36W/LED	无	15	无
SZ 2500.210	11W	24× 0.36W/LED	无	10	有
SZ 2500.211	11W	24× 0.36W/LED	无	10	有
SZ 2500.212	11W	24× 0.36W/LED	无	10	有
SZ 2500.213	11W	24× 0.36W/LED	无	10	有

以上所有型号均为 100-230V~ 50/60Hz、非用户替换光源、吸顶式/壁式, LED 控制装置, I 类, ta: -20...+55° C, IP20, 电气结构以及安全和电磁兼容有关的关键件均一致。



CHINA QUALITY CERTIFICATION CENTRE



中国国家强制性产品认证证书

证书编号: 2016011001924336

发证日期: 2023年01月11日

有效期至: 2027年11月01日

认证委托人名称 及注册地址	Rittal GmbH & Co. KG Auf dem Stützelberg, D-35745 Herborn, 德国
产品生产者名称 及注册地址	STEINEL GmbH Dieselstrasse 80-84, 33442 Herzebrock-Clarholz, 德国
生产企业名称 及生产地址	STEINEL Electronic S.R.L. Str. Ramnicu Valcea Nr. 79-115300 Curtea de Arges, 罗马尼亚
产品名称和系列、 规格、型号	固定式灯具 (吸顶式/壁式, LED 模块用交流电子控制装置, II类, IP20, 适宜直接安装在普通可燃材料表面, ta:55°C) 见附件: 100-230V ~ 50/60Hz
产品标准和 技术要求	GB/T 17743-2021;GB 7000.1-2015;GB 7000.201-2008

上述产品符合 CNCA-C10-01:2014 认证规则的要求, 特发此证。

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

本证书为变更证书, 证书首次颁发日期: 2016年12月01日

经中国合格评定国家认可委员会认可 CNAS C001-P

可通过扫描下方二维码或登录国家认监委网站 (www.cnca.gov.cn) 查验证书信息



签发:

谢肇煦



中国质量认证中心



中国国家强制性产品认证证书

证书编号：2016011001924336

第 1 页 共 1 页

本证书及附件应同时使用，信息查验说明见证书页

纸号：

型号	额定功率	光源功率	感应器	环路最多安装样品数量(个)	插座
SZ 2500.310	13W	32× 0.36W/LED	有	10	有
SZ 2500.311	13W	32× 0.36W/LED	有	10	有
SZ 2500.312	13W	32× 0.36W/LED	有	10	有
SZ 2500.313	13W	32× 0.36W/LED	有	10	有
SZ 2500.300	13W	32× 0.36W/LED	有	15	无
SZ 2500.200	11W	24× 0.36W/LED	无	15	无
SZ 2500.210	11W	24× 0.36W/LED	无	10	有
SZ 2500.211	11W	24× 0.36W/LED	无	10	有
SZ 2500.212	11W	24× 0.36W/LED	无	10	有
SZ 2500.213	11W	24× 0.36W/LED	无	10	有

以上所有型号均为 100-230V~ 50/60Hz、非用户替换光源、吸顶式/壁式，LED 控制装置，I 类，ta：-20...+55° C，IP20，电气结构以及安全和电磁兼容有关的关键件均一致。



中国质量认证中心