

Rittal – The System.

Faster – better – everywhere.

▶ WM Wallmount Enclosures



Rittal WM enclosures set the standard for maximum use of space and ease of installation. WM compact enclosures can be used for virtually any application. NEMA protection ratings are ensured through a secure locking system, foamed-in-place gasket and knife-edge perimeter. Features include a body constructed of cold rolled steel, steel doors and zinc-plated mounting panels. WM enclosures are readily available in all of the most popular sizes, protection categories and configurations – including universal disconnect cutout.

For complete details on the entire line, go to www.rittal.us.

- One-piece welded cold-rolled steel body
- Available in carbon and stainless steel
- Zinc-plated mounting panel standard
- Available with universal disconnect cutout
- Foamed-in-place gasket
- Quick-release hidden 130° door hinges
- Electrophoresis dip-coat primer with powder-coat surface
- Flange-trough collar opening channels liquids and dust away from enclosure gasket and enclosure interior
- Left-hand hinged door (the single door configuration is reversible)
- Wall-mounting holes
- Single door enclosures less than 20" in height have one ¼ turn latch with screwdriver insert
- Single door enclosures 20 - 40" in height have two ¼-turn latches with screwdriver inserts
- Single door enclosures greater than or equal to 42" in height have a 3-point latching L-handle
- Double door and disconnect enclosures have a 2- or 3-point latching L-handle

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES



Carbon Steel, Single Door – UL/cUL Type 12, 3R, 4

Part No.	Catalog No.	H x W x D
8017528	WM121206NC	12x12x6
8017529	WM161206NC	16x12x6
8017530	WM161606NC	16x16x6
8017531	WM162006NC	16x20x6
8017532	WM201606NC	20x16x6
8017533	WM202006NC	20x20x6
8017534	WM241606NC	24x16x6
8017535	WM242006NC	24x20x6
8017536	WM242406NC	24x24x6
1034250	WM161208NC	16x12x8
1244250	WM161608NC	16x16x8
8017541	WM162008NC	16x20x8
1045250	WM201608NC	20x16x8
1050250	WM202008NC	20x20x8
8017544	WM202408NC	20x24x8
8017545	WM241608NC	24x16x8
8017546	WM242008NC	24x20x8
1060250	WM242408NC	24x24x8
8017549	WM243008NC	24x30x8
8017551	WM302008NC	30x20x8
1076250	WM302408NC	30x24x8
1077250	WM303008NC	30x30x8
8017554	WM362408NC	36x24x8
8017559	WM423608NC	42x36x8
8017560	WM483608NC	48x36x8
8018963	WM202010NC	20x20x10
9851538	WM241610NC	24x16x10
8017561	WM242010NC	24x20x10
8017555	WM363008NC	36x30x8
8017557	WM363608NC	36x36x8
8017558	WM423008NC	42x30x8
8017562	WM242410NC	24x24x10
8017563	WM302410NC	30x24x10
8018902	WM303010NC	30x30x10
8017566	WM362410NC	36x24x10
8017567	WM363010NC	36x30x10
8017569	WM423610NC	42x36x10
8017570	WM483610NC	48x36x10
8017571	WM603610NC	60x36x10
1350250	WM202012NC	20x20x12
8017574	WM242012NC	24x20x12
8017575	WM242412NC	24x24x12
8017576	WM302412NC	30x24x12
1073250	WM303012NC	30x30x12
8017578	WM362412NC	36x24x12
8017579	WM363012NC	36x30x12
8017581	WM363612NC	36x36x12
8017586	WM423612NC	42x36x12

Carbon Steel, Single Door – UL/cUL Type 12, 3R, 4 (continued)

Part No.	Catalog No.	H x W x D
8017588	WM483612NC	48x36x12
8017591	WM603612NC	60x36x12
8017594	WM363016NC	36x30x16
8017595	WM483616NC	48x36x16
8017597	WM603616NC	60x36x16
8017598	WM302420NC	30x24x20
8017599	WM483620NC	48x36x20

Carbon Steel, Double Door – UL/cUL Type 12

Part No.	Catalog No.	H x W x D
8017550	WM244208NC	24x42x8
8017564	WM304210NC	30x42x10
8017565	WM304810NC	30x48x10
8017582	WM364212NC	36x42x12
8017583	WM364812NC	36x48x12
8017584	WM366012NC	36x60x12
8017587	WM426012NC	42x60x12
8017590	WM484812NC	48x48x12

Carbon Steel, Single Door, Without Mounting Panel – UL/cUL Type 12, 3R, 4

Part No.	Catalog No.	H x W x D
9851533	WM242408NC L/MPL	24x24x8
9851534	WM302408NC L/MPL	30x24x8
9851535	WM303008NC L/MPL	30x30x8
9851536	WM363008NC L/MPL	36x30x8

Carbon Steel Disconnect – UL/cUL Type 12, 3R, 4

Part No.	Catalog No.	H x W x D
8018976	WM202208XC	20x22x8
8018977	WM242208XC	24x22x8
8017548	WM242608XC	24x26x8
9851539	WM242610XC	24x26x10
8018978	WM302608XC	30x26x8
8017556	WM363208XC	36x32x8
8017568	WM363210XC	36x32x10
8017572	WM603810XC	60x38x10
8018979	WM302612XC	30x26x12
8017580	WM363212XC	36x32x12
8017585	WM423212XC	42x32x12
8018980	WM423812XC	42x38x12
8017589	WM483812XC	48x38x12
8017592	WM603812XC	60x38x12
8017596	WM483816XC	48x38x16
8018981	WM603816XC	60x38x16

Note: measurements are approximate.

Rittal North America LLC

Woodfield Corporate Center • 425 North Martingale Road,
Suite 400 • Schaumburg, Illinois 60173 • USA
Phone: 937-399-0500 • Toll-free: 800-477-4000
Email: rittal@rittal.us • Website: www.rittal.us