

Rittal – The System.

Faster – better – everywhere.



TS IT PRO 24U

TS IT Pro 24U

The TS IT Pro 24U enclosure is a perfect solution for commercial, education, and government applications. By combining a space-saving size with robust construction, this enclosure easily meets the same standards required for data centers scaled for local deployments. Featuring a fully welded frame and tool-less, snap-in installation technology, the TS IT Pro 24U is easily configured to optimize operating efficiency. When compared to a full-size rack, this enclosure is a great fit for smaller server setups or to keep switches and routers secure while saving both cost and space. Engineered by Rittal and manufactured in the USA, the TS IT Pro 24U offers dependable quality that lasts.

TS IT Pro Benefits

The Rittal TS IT Pro is a robust secure enclosure to keep your IT assets safe while providing a flexible and easily reconfigurable platform to meet the demands of tomorrow.

- Quality design: made in the USA
- Easy to order, ready to ship: Easily configured for your application complete with accessories
- Flexible installation: Quick-release, easy-to-remove doors increase workspace area; vertical rails easily adjust to accommodate varying depths of equipment
- Fully welded frame: Built for long-term use with a fully welded frame while future-proofing IT asset swaps and refreshes



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES



TS IT PRO 24U

The TS IT Pro 24U is configured for rapid deployment. Enclosures are complete with depth-adjustable 19" EIA rails, casters, and locking front and rear perforated doors. Available with or without sidewalls.



Includes:

- Perforated single steel door at the front and rear (85% perforated); 145° quick-release security hinges
- Roof cable access
- Front and rear handles with keyed locks
- Removable casters
- Leveling feet
- Fully welded steel frame
- 19" EIA rails printed with U markings on the front and back of each rail
- M6 cage nuts (package of 50)
- M6 mounting screws (package of 50)
- Solid sidewalls

Material:

- Carbon steel

Color:

- Black RAL 9005

Certifications:

- UL 60950-1
- EIA 310E
- UL 2416
- cUL

Warranty:

- 5 years



TS IT Pro 24U with Side Panels

Part Number	RU Height	Height with Casters	Width	Depth	Door Type	Weight Capacity (Static)	Net Weight of Each Rack	Color
9982.200	24U	49" (1254 mm)	24" (600 mm)	42" (1070 mm)	Perforated front and rear	3000 lb.	173 lb	Black

TS IT Pro 24U without Side Panels

Part Number	RU Height	Height with Casters	Width	Depth	Door Type	Weight Capacity (Static)	Net Weight of Each Rack	Color
9982.201	24U	49" (1254 mm)	24" (600 mm)	42" (1070 mm)	Perforated front and rear	3000 lb.	138 lb	Black

TS IT Pro 24U Cable Management Accessories

Part Number	Description	Dimension	Color	Packs of
9969.736	Horizontal Cable Management with Hingeable/Removeable Cover	1U	Black	2
9969.597	Horizontal Cable Management with Hingeable/Removeable Cover	2U	Black	2
9969.599	Quarter-turn Cable Managers Fastener Strap	17"	Black	10
9969.600	Quarter-turn Cable Managers Collection Claw	3" x 4.4"	Black	10
9961.779	Quarter-turn Cable Managers D-ring	3.5" x 1.75"	Black	10
9961.780	Quarter-turn Cable Managers D-ring	5" x 3.5"	Black	10
5302.202	Cable Entry Panel with Brush Strip	1U	Black	1

Rittal LLC

Woodfield Corporate Center
 425 North Martingale Road, Suite 400 • Schaumburg, Illinois 60173 • USA
 Phone: 937-399-0500 • Toll-free: 800-477-4000
 Email: rittal@rittal.us • Online: www.rittal.com

