

The new 3-part AX wall-mounted enclosure – less complexity, more flexibility



Robust design, versatile use

Discover the new three-part AX wall-mounted enclosure for added flexibility plus optimised system integration. The basic enclosure offers numerous possibilities, and combining it with the Rittal system opens up further benefits.

Conversion assistant – new 3-part AX wall-mounted enclosure

Model No.	Article designation	Dimension [mm]			U	Model No. new	Article designation new	Note
		Width	Height	Depth				
2253.605	EL wall-mounted enclosure, 3-part with mounting plate and mounting angles, static installation	600	212	473	3	-	-	This enclosure is omitted without replacement.
2243.605	EL wall-mounted enclosure, 3-part with mounting plate and mounting angles, static installation	600	212	373	3	-	-	This enclosure is omitted without replacement.
2256.605	EL wall-mounted enclosure, 3-part with mounting plate and mounting angles, static installation	600	345	473	6	2260.640	AX wall-mounted enclosure, 3-part, 6 U	The mounting plate is omitted from the scope of supply. If required, it can be replaced by a KX mounting plate.
2246.605	EL wall-mounted enclosure, 3-part with mounting plate and mounting angles, static installation	600	345	373	6	2260.630	AX wall-mounted enclosure, 3-part, 6 U	
2259.605	EL wall-mounted enclosure, 3-part with mounting plate and mounting angles, static installation	600	478	473	9	2260.940	AX wall-mounted enclosure, 3-part, 9 U	
2249.605	EL wall-mounted enclosure, 3-part with mounting plate and mounting angles, static installation	600	478	373	9	2260.930	AX wall-mounted enclosure, 3-part, 9 U	
2262.605	EL wall-mounted enclosure, 3-part with mounting plate and mounting angles, static installation	600	612	473	12	2261.240	AX wall-mounted enclosure, 3-part, 12 U	
2252.605	EL wall-mounted enclosure, 3-part with mounting plate and mounting angles, static installation	600	612	373	12	2261.230	AX wall-mounted enclosure, 3-part, 12 U	The mounting plate is omitted from the scope of supply. If required, it can be replaced by a KX mounting plate.
2265.605	EL wall-mounted enclosure, 3-part with mounting plate and mounting angles, static installation	600	746	473	15	2261.540	AX wall-mounted enclosure, 3-part, 15 U	
2255.605	EL wall-mounted enclosure, 3-part with mounting plate and mounting angles, static installation	600	746	373	15	-	-	This enclosure is omitted without replacement.



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

Conversion assistant – new 3-part AX wall-mounted enclosure

Model No.	Article designation	Dimension [mm]			U	Model No. new	Article designation new	Note
		Width	Height	Depth				
2261.605	EL wall-mounted enclosure, 3-part with mounting plate and mounting angles, static installation	600	1012	373	21	2262.130	AX wall-mounted enclosure, 3-part, 21 U	The mounting plate is omitted from the scope of supply. If required, it can be replaced by a KX mounting plate.
2271.605	EL wall-mounted enclosure, 3-part with mounting plate and mounting angles, static installation	600	1012	473	21	2262.140	AX wall-mounted enclosure, 3-part, 21 U	
7706.135	EL wall-mounted enclosure, 3-part with punched rails and mounting angles, depth-adjustable	600	345	473	6	2260.640	AX wall-mounted enclosure, 3-part, 6 U	The C rails are omitted from the scope of supply. If required, they can be replaced by the 30/15 C rail or, depending on the application, by support strips or 14 x 39 mm VX punched sections with mounting flange from the system accessories.
7709.135	EL wall-mounted enclosure, 3-part with punched rails and mounting angles, depth-adjustable	600	478	473	9	2260.940	AX wall-mounted enclosure, 3-part, 9 U	
7712.135	EL wall-mounted enclosure, 3-part with punched rails and mounting angles, depth-adjustable	600	612	473	12	2261.240	AX wall-mounted enclosure, 3-part, 12 U	
7715.135	EL wall-mounted enclosure, 3-part with punched rails and mounting angles, depth-adjustable	600	746	473	15	2261.540	AX wall-mounted enclosure, 3-part, 15 U	
7715.735	EL wall-mounted enclosure, 3-part with punched rails and mounting angles, depth-adjustable	600	746	573	15	2261.550	AX wall-mounted enclosure, 3-part, 15 U	
7721.135	EL wall-mounted enclosure, 3-part with punched rails and mounting angles, depth-adjustable	600	1012	473	21	2262.140	AX wall-mounted enclosure, 3-part, 21 U	
7709.535	EL wall-mounted enclosure, 3-part, preassembled with mounting angles, depth-adjustable	600	478	673	9	2260.960	AX wall-mounted enclosure, 3-part, 9 U	The outlet filters, C rails and the earth rail are omitted from the scope of supply. These components can be ordered as required from our range of system accessories.
7709.735	EL wall-mounted enclosure, 3-part, preassembled with mounting angles, depth-adjustable	600	478	573	9	2260.950	AX wall-mounted enclosure, 3-part, 9 U	
7715.535	EL wall-mounted enclosure, 3-part, preassembled with mounting angles, depth-adjustable	600	746	673	15	2261.560	AX wall-mounted enclosure, 3-part, 15 U	
7721.535	EL wall-mounted enclosure, 3-part, preassembled with mounting angles, depth-adjustable	600	1012	673	21	2262.160	AX wall-mounted enclosure, 3-part, 21 U	
7721.735	EL wall-mounted enclosure, 3-part, preassembled with mounting angles, depth-adjustable	600	1012	573	21	2262.150	AX wall-mounted enclosure, 3-part, 21 U	

Matching model numbers for accessories for 3-part AX wall-mounted enclosure

Gland plates for 3-part AX wall-mounted enclosure	
Model No.	Designation
2260.060	With brush strip
2260.070	With metric knockouts

KX mounting plates		
Model No.	Width x height [mm]	Configuration options
1565.800	485 x 175	Depending on the enclosure, the following mounting plates can be used for a maximum configuration: enclosure height 6 U: 1 x 1569.800 enclosure height 9 U: 2 x 1565.800 enclosure height 12 U: 2 x 1569.800 enclosure height 15 U: 4 x 1565.800 enclosure height 21 U: 1 x 1569.800 and 4 x 1565.800
1569.800	485 x 275	

VX punched section with mounting flange, 14 x 39 mm	
Model No.	For installation in
8619.700	437 mm deep enclosure
8619.710	573 mm deep enclosure
8619.720	673 mm deep enclosure or in the width of the wall section

Support strip	
Model No.	For installation in
4594.000	437 mm deep enclosure
4309.000	573 mm deep enclosure
4596.000	673 mm deep enclosure or in the width of the wall section

Earth rail, horizontal	
Model No.	For installation in
7113.000	The width of the wall section

30/15 C rail in accordance with EN 60715		
Model No.	Length [mm]	Note
4943.000	455	Depending on the installation, the rails must be cut to length in the width or depth.
4944.000	555	
4945.000	755	
4946.000	955	
4947.000	1155	

Blue e+ outlet filter		
Model No.	Suitable for	Colour
3238.300	Centre part of the wall-mounted enclosure	RAL 7035
3238.308	Centre part of the wall-mounted enclosure	RAL 9005

Contact:

www.rittal.com/contact