


Apparatskap

Skapsystemer


Gulvskap rekkemontert VX25

Elektronikkenskap


Forfra uten frontramme




Snitt A – A




Detalj X



Detalj Y



Snitt B – B



Best.nr.	Høydemål						Dybdemål		
	H1 mm	H2		H3 mm	H4		H5 mm	T1 mm	T2 mm
		mm	U		mm	U			
8410.000	1608	1466,6	33	i. L. 1511	1422,4	32	1375	619,5	i. L. 511
8418.000	1608	1466,6	33	i. L. 1511	1422,4	32	1375	819,5	i. L. 711
8430.000	2008	1866,9	42	i. L. 1911	1822,45	41	1625	619,5	i. L. 511
8438.000	2008	1866,9	42	i. L. 1911	1822,45	41	1625	819,5	i. L. 711