


W [mm]	H [mm]	Best.-Nr. Model No. Référence
1000	400	9683.604
1000	600	9683.606
1000	800	9683.608
1200	400	9683.624
1200	600	9683.626
1200	800	9683.628
400	200	9683.642
400	300	9683.643
400	400	9683.644
400	600	9683.646
400	800	9683.648
600	1000	9683.660
600	1500	9683.661
600	200	9683.662
600	300	9683.663
600	400	9683.664
600	600	9683.666
600	800	9683.668
600	1200	9683.672
600	1400	9683.674
600	1600	9683.676
600	1800	9683.678
800	1000	9683.680
800	1500	9683.681
800	200	9683.682
800	300	9683.683
800	400	9683.684
800	600	9683.686
800	800	9683.688
800	1200	9683.692
800	1400	9683.694
800	1600	9683.696
800	1800	9683.698



W [mm]	H [mm]	Best.-Nr. Model No. Référence
600	150	9683.561
600	200	9683.562
600	300	9683.563
600	400	9683.564




www.rittal.com

SV

9683.5xx


9683.6xx

4x



M8x16

14x




M5x12

4x



M8

1x



M8x30

1x



M8

1x



A8,4

1x



Ø 8,2x16

1x



M8

2x



