

Rittal – The System.

Faster – better – everywhere.



SZ 2500.714 Socket box

State: 2024-10-19 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2500.714 - Socket box for LED System Light

In combination with the LED system light, the socket box creates a flexible modular system for international use.

Features

Model No.	SZ 2500.714
Product description	In combination with the LED system light, the socket box creates a flexible modular system for international use.
Benefits	Similar connection accessories as for LED system lights Cascadable with LED system light Flexible mounting possible throughout the enclosure and on the tubular door frame Ergonomic positioning of the socket box on surfaces No additional wiring required, due to simple connection technology and integration of the LED system light into the circuit
Material	Plastic
Color	RAL 7016
Supply includes	Assembly components
Connection options	Power Supply, 3-pole Through-wiring, 3-pole
Protection category	II (total insulation)
Note	Through-wiring or a 3-pole infeed is necessary depending on the application
Dimensions	Width: 163 mm Height: 68 mm Depth: 43.5 mm
Operating temperature range	-20 °C...55 °C
Outlets	USA/CDN (type B, NEMA 5-15)
Rated operating voltage	100 V - 125 V, 1~, 50 Hz/60 Hz
Packaging unit	1 pc(s).
Weight/packaging unit	0.247 kg

Features

Net weight	0.24
Gross weight	0.247
Customs tariff number	85366990
EAN	4028177956841
ETIM 8	EC000330
ETIM 7.0	EC000330
ECLASS 8.0	27142604

Approvals

Approvals	UR + C-UR (recognized)
Explanations	Declaration of conformity