

Rittal – The System.

Faster – better – everywhere.



SZ 4139.150 Courtesy light

State: 2024-09-27 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 4139.150 - Courtesy light

Supply voltage: 100 - 240 V AC 50/60 Hz

Features

Model No.	SZ 4139.150
Version	with door-operated switch
Supply includes	Courtesy light Light (bulb) Light cover Assembly components Integral door-operated switch
Rated power	14 W
Ballast	Wide range voltage EB
Connection options	Power supply through connector Through-wiring (configuration of row of luminaires)
Integral door-operated switch	Yes
Light (bulb)	Fluorescent lamp, G13 backplate
Protection category	I (PE conductor)
Switch (type)	Integral, on/off/door-operated switch mode
Light cover	Yes
Light – installation type	Screw fastening
Rated impulse withstand voltage, phase to earth	1000 V AC
Rated impulse withstand voltage, phase to phase	500 V AC
Rated insulation voltage	500 V DC/1s
Installation options	TS horizontal profile from roof frames: direct TS, SE vertical section: with TS adapter bracket SE sections on front and rear of roof frame: with TS adapter bracket SE profiles to the side of roof frames: direct

Features

Dimensions	Width: 452 mm Height: 117 mm Depth: 50 mm
Operating temperature range	-15 °C...45 °C
Outlets	D, ground contact (type F, CEE 7/4)
Storage temperature range	-20 °C...70 °C
Rated operating voltage	100 V - 240 V, 1~, 50 Hz/60 Hz
Socket version	D, ground contact (type F, CEE 7/4)
Packaging unit	1 pc(s).
Weight/packaging unit	2.02 kg
Net weight	1.25
Gross weight	1.319
Customs tariff number	94054990
EAN	4028177320741
ETIM 7.0	EC000321
ECLASS 8.0	27189241

Approvals

Explanations	Declaration of conformity Declaration of conformity UK
--------------	---