

Rittal – The System.

Faster – better – everywhere.



CS 9791.035

Outdoor Wall-mounted enclosure

State: 2024-09-27 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CS 9791.035 - Outdoor Wall-mounted enclosure

Outdoor housings for wall or pole mounting. Enclosure-within-an-enclosure concept, outer enclosure with cut-out at the bottom and integrated louvers on the rear and side panels for ventilation.

Features

Model No.	CS 9791.035
Product description	Outdoor housings for wall or pole mounting. Housing-within-a-housing concept, outer enclosure with cut-out at the bottom and integrated louvers on the rear and side panels for ventilation
Material	Enclosure and mounting plate: Aluminum AlMg3 Door inner casing: Stainless steel 1.4301 (AISI 304)
Surface finish	Housing: powder-coated, UV-resistant pure polyester
Color	RAL 7035
Supply includes	Double-walled outdoor housing, fully preconfigured Inner enclosure with mounting plate, gland plate and security lock Mounting bracket for enclosure internal thermostat or hygostat Outer housing with designer cover and security lock 3524 E 2 C rails on the rear panel
Dimensions	Width: 530 mm Height: 700 mm Depth: 265 mm
Clearances	Clearance width: 440 mm Clearance height: 545 mm Clearance depth: 195 mm
Dimensions of mounting plate (W x H)	430 mm x 535 mm
Inner housing	Width: 460 mm Height: 565 mm Depth: 220 mm
Lock	Lock version: Cam No. of locks: 2

Features

Protection category IP to IEC 60529	IP 55
-------------------------------------	-------

Note	Delivery times on request.
------	----------------------------

Base material	Aluminum
---------------	----------

Packaging unit	1 pc(s).
----------------	----------

Weight/packaging unit	14.86 kg
-----------------------	----------

Net weight	16.625
------------	--------

Gross weight	17.5
--------------	------

Customs tariff number	94032080
-----------------------	----------

EAN	4028177193710
-----	---------------

ETIM 7.0	EC000261
----------	----------

ECLASS 8.0	27180101
------------	----------

Approvals

Explanations	Declaration of conformity Declaration of conformity UK
--------------	---