

Rittal – The System.

Faster – better – everywhere.



KL 1522.010

接线箱 KL

状态: 2024-9-27 (来源: rittal.com/cn-zh)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



KL 1522.010 - 接线箱 KL 不锈钢

接线盒，不锈钢 1.4301 (AISI 304)。防护等级：IP 66。

特征

型号	KL 1522.010
材料	箱体：不锈钢 1.4301 (AISI 304) 箱盖：不锈钢 1.4301 (AISI 304) ，周围用发泡聚氨酯塑料 (PU) 密封圈
表面	箱体和箱盖：拉丝，粒度 180
供货范围	箱体配有箱盖 含塑料插口的快换螺纹接口
Protection category NEMA	NEMA 4X
防护等级 IP，符合 EN 60 529 标准	IP 66
IK 编码	IK08
尺寸	宽度: 300 mm 高度: 150 mm 深度: 80 mm
箱盖材料厚度	1.25 mm
箱体材料厚度	1.25 mm
锁	锁具数量: 4
基本材料	不锈钢 1.4301 (AISI 304)
包装单元	1 件
重量/包装	1.8 kg
净重	1.673

特征

毛重	1.94
税率号	84879090
EAN	4028177008465
E-Number Sweden	E3404364
ETIM 8	EC000261
ETIM 7.0	EC000261
ECLASS 8.0	27180101

批准

批准	Bureau Veritas DNV-GL Lloyds Register of Shipping UL + C-UL (listed)
解释	符合性声明 符合性声明 UK