

Rittal – The System.

Faster – better – everywhere.



HD 2410.010 Cable gland HD

State: 19/10/2024 (Source: rittal.com/com-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



HD 2410.010 - Cable gland HD

HD cable gland IP 68 (5 bar, 30 min.)



Features

Model No.	HD 2410.010
Design	Standard
Benefits	Smooth, solid exterior surfaces effectively prevent the depositing of harmful micro-organisms. Much easier, and therefore cheaper to clean compared with conventional cable glands.
Applications	Manufacturer Clean room technology (e.g. pharmaceuticals) Biotechnology Chemical industry
Material	Nut: Stainless steel 1.4305 (AISI 303) Seal: Conforms to FDA 21 CFR 177.2600
Dimensions	Thread: M16 x 1.5
For cable diameters	5 - 10 mm
Operating temperature range	-20 °C...100 °C

Features

IP protection category to IEC 60529	IP 68 (5 bar, 30 min)
Packs of	5 pc(s).
Weight/pack	0.205 kg
Net weight	0.195
Gross weight	0.221
Customs tariff number	73181900
EAN	4028177022454
E-Number Sweden	E3465025
ETIM 7.0	EC000441
ECLASS 8.0	27149109

Approvals

Explanations	Manufacturer's declaration
--------------	----------------------------