

**Rittal – The System.**

Faster – better – everywhere.



**SZ 2562.200**

**Plastic gland plate, modular**

State: 27/09/2024 (Source: [rittal.com/com-en](http://rittal.com/com-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SZ 2562.200 - Plastic gland plate, modular with metric knockouts, for AX

Simply break through the plastic on the knockouts for cable glands. Additional rectangular cut-outs and reinforcement frame allow the cable gland to be installed directly (modular).

## Features

Model No.	SZ 2562.200
Product description	Simply break through the plastic on the knockouts for cable glands. Additional rectangular cut-outs and reinforcement frame allow the cable gland to be installed directly (modular).
Material	Plastic to UL 94-V0
Colour	RAL 7035
Number of rectangular cutouts information	1 rectangular cut-out can hold 10 small seal inserts
Number of rectangular cutouts	3
Note	The allocation of gland plate sizes is indicated on the relevant enclosures
No. of metric knockouts	3 x M12 2 x M16 3 x M20 3 x M25 2 x M32
Dimensions	Width: 339 mm Depth: 149 mm
To fit	Enclosure type: AX
Gland plate	Size: 2
Operating temperature range	-40 °C...80 °C
Protection category to IEC 60 529	IP 66 if installed correctly
Type rating to UL 50E	Type 1 Type 12

# Features

---

Number knockouts	3
	2
	3
	3
	2

---

Metric diameter	M12
	M16
	M20
	M25
	M32

---

Packs of	1 pc(s).
----------	----------

---

Weight/pack	0.332 kg
-------------	----------

---

Net weight	0.3
------------	-----

---

Gross weight	0.332
--------------	-------

---

Customs tariff number	39269097
-----------------------	----------

---

EAN	4028177938403
-----	---------------

---

ETIM 8	EC000211
--------	----------

---

ETIM 7.0	EC000211
----------	----------

---

ECLASS 8.0	27142421
------------	----------

---

# Approvals

---

Approvals	UL + C-UL - FTTA
-----------	------------------