

Rittal – The System.

Faster – better – everywhere.



AX 2573.100 Metal gland plate

State: 30/06/2024 (Source: rittal.com/com-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AX 2573.100 - Metal gland plate with metric knockouts, for AX

Simply knock out the holes for the cable glands using a screwdriver.

Features

Model No.	AX 2573.100
Product description	Simply knock out the holes for the cable glands using a screwdriver.
Material	Sheet steel
Colour	RAL 7035
Note	The allocation of gland plate sizes is indicated on the relevant enclosures
No. of metric knockouts	4 x M12 4 x M16 7 x M20 15 x M25 2 x M32 2 x M40
Dimensions	Width: 447 mm Depth: 149 mm
To fit	Enclosure type: AX
Gland plate	Size: 3
Protection category to IEC 60 529	IP 66 if installed correctly
Type rating to UL 50E	Type 1 Type 12K
Number knockouts	4 4 7 15 2 2

Features

Metric diameter	M12
	M16
	M20
	M25
	M32
	M40

Packs of	1 pc(s).
----------	----------

Weight/pack	1.07 kg
-------------	---------

Customs tariff number	73269098
-----------------------	----------

EAN	4028177925205
-----	---------------

E-Number Sweden	E3465297
-----------------	----------

ETIM 7.0	EC000211
----------	----------

ECLASS 8.0	27142421
------------	----------

Approvals

Approvals	UL + C-UL - FTTA
-----------	------------------