

# Rittal – The System.

Faster – better – everywhere.



## AX 2574.100 Metal gland plate

State: 26/09/2024 (Source: [rittal.com/com-en](http://rittal.com/com-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AX 2574.100 - Metal gland plate with metric knockouts, for AX

Simply knock out the holes for the cable glands using a screwdriver.

## Features

Model No.	AX 2574.100
Product description	Simply knock out the holes for the cable glands using a screwdriver.
Material	Sheet steel
Colour	RAL 7035
Note	The allocation of gland plate sizes is indicated on the relevant enclosures
No. of metric knockouts	1 x M12 6 x M16 8 x M20 11 x M25 6 x M32 4 x M40
Dimensions	Width: 534 mm Depth: 149 mm
To fit	Enclosure type: AX
Gland plate	Size: 4
Protection category to IEC 60 529	IP 66 if installed correctly
Type rating to UL 50E	Type 1 Type 12K
Number knockouts	1 6 8 11 6 4

# Features

---

Metric diameter	M12 M16 M20 M25 M32 M40
Packs of	1 pc(s).
Weight/pack	1.28 kg
Net weight	0.98
Gross weight	0.98
PCF/PU (Cradle-to-Gate)	4.9 kg CO2 eq (Cat B)
Note on the PCF class	Category B: PCF value (cradle-to-gate) approximated based on product weight and self-declared
Customs tariff number	73269098
EAN	4028177925212
E-Number Sweden	E3465298
ETIM 8	EC000211
ETIM 7.0	EC000211
ECLASS 8.0	27142421

# Approvals

---

Approvals UL + C-UL - FT TA