

Rittal – The System.

Faster – better – everywhere.



SK 3240.200 Outlet filter

State: 01/09/2024 (Source: [rittal.com/com-en](https://www.rittal.com/com-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3240.200 - Outlet filter Standard

For ventilation by convection, an outlet filter can be fitted in both the upper and lower sections of the enclosure.



Features

Model No.	SK 3240.200
Product description	For ventilation by convection, an outlet filter can be installed in the upper and lower sections of the enclosure.
Material	ABS
Colour	RAL 7035
Supply includes	Outlet filter Chopped-fibre filter mat
Mounting cut-out	Cut-out width: 224 mm Cut-out height: 224 mm
To fit Model No.	3240.1xx/3240.5xx/3241.1xx/3241.5xx
Dimensions	Width: 255 mm Height: 255 mm Depth: 25 mm
Protection category NEMA	Type 12 with chopped-fibre filter/pleated filter Type 3 Type 3R Type 4 Type 4X with chopped-fibre filter - pleated filter and hose-proof hood
IP protection category to IEC 60529	IP54 with chopped-fibre filter/pleated filter IP55 with pleated filter and absorber mat IP56 with chopped-fibre filter/pleated filter and hose-proof hood

Features

Weight/pack	0.56 kg
Packs of	1 pc(s).
Customs tariff number	39269097
EAN	4028177651975
E-Number Sweden	E3404361
ETIM 8	EC002513
ETIM 7.0	EC002513
ECLASS 8.0	27180706

Approvals

Approvals	CSA UL + C-UL - FTTA UR + C-UR (recognized)
Certificates	EAC
Explanations	Declaration of conformity