

Rittal – The System.

Faster – better – everywhere.



HD 4000.080 Viewing window HD

State: 30/06/2024 (Source: rittal.com/com-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



HD 4000.080 - Viewing window HD

For the protection of switches or displays.

Features

Model No.	HD 4000.080
Product description	For the protection of switches or displays.
Benefits	Large viewing panel Gap-free transition between the viewing window and the frame External hinge With T handle for easy opening without a key
Material	Frame: Stainless steel 1.4301 (AISI 304) Seal: Silicone, compliant with FDA Guideline 21 CFR 177.2600 Viewing window: Polycarbonate
Supply includes	2 hinges T handle Assembly parts
Visible area	Viewing window width: 410 mm Viewing window height: 320 mm
Dimensions	Width: 518 mm Height: 436 mm Depth: 23 mm
To fit	Enclosure type: HD compact enclosure
IP protection category to IEC 60529	IP 55
Protection category NEMA	NEMA 12
Installation options	For external mounting on surfaces.
Packs of	1 pc(s).
Weight/pack	3.94 kg
Customs tariff number	39252000
EAN	4028177697041

Features

ETIM 8	EC002527
ETIM 7.0	EC002527
ECLASS 8.0	27181002
