


Rittal – The System.

Faster – better – everywhere.



AS 4050.747

Wire end ferrules

State: 07/10/2024 (Source: rittal.com/com-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4050.747 - Wire end ferrules on a reel

With plastic collar.

Features

Model No.	AS 4050.747
Product description	With plastic collar.
Technical specifications	Heat-resistant to 105 °C
Material	E-Cu, galvanic tin-plated Plastic collar: Polypropylene
Colour	Grey
Length	8 mm
AWG	18
Internal diameter	2.8 mm
For cross-section	0.75 mm ²
DIN colour code	Yes
Note	UL-certified in conjunction with the relevant tools, such as crimping machines.
Standards	AEH DIN 46228
Delivery form	Taped
Packs of	5,000 pc(s).
Weight/pack	5 kg
Net weight	5
Customs tariff number	85369010
EAN	4028177805156
ETIM 8	EC000005
ETIM 7.0	EC000005
ECLASS 8.0	36659290

Approvals

Approvals

UL + C-UL (listed)

UR