


Rittal – The System.

Faster – better – everywhere.



AS 4052.142 Screwdrivers

State: 07/10/2024 (Source: rittal.com/com-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4052.142 - Screwdrivers insulated

With a long, slender handle and high-performance tip with non-transfer insulation.

Features

Model No.	AS 4052.142
Design	Isolation protection 1000 V For plus/minus
Product description	With a long, slender handle and high-performance tip with non-transfer insulation.
Benefits	Minimal force required, thanks to ergonomically styled handle Handle head with anti-roll protection and clear screw labelling Black coated blade tip to preserve precision and accuracy of fit Handle 30% and insulation up to 50% slimmer than comparable tools Optimum interconnection of hand and handle supports higher torques and longer, fatigue-free working
Material	Blade: Chrome-molybdenum-vanadium alloy Handle core: Hard plastic Handle body: Elastic, highly flexible plastic
Colour	Handle: Anthracite and Rittal Power Pink
Blade dia.	6 mm
Blade length	100 mm
Blade tip	Z 2
Handle dia.	27 mm
Handle length	115 mm
Standards	IEC 60 900
Packs of	1 pc(s).
Weight/pack	0.073 kg
Net weight	0.07
Gross weight	0.077

Features

Customs tariff number	82054000
EAN	4028177807303
ETIM 8	EC000144
ETIM 7.0	EC000144
ECLASS 8.0	21040406
