

**Rittal – The System.**

Faster – better – everywhere.



# AS 4054.140

## Crimping pliers

State: 07/10/2024 (Source: [rittal.com/com-en](http://rittal.com/com-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4054.140 - Crimping pliers for ring terminals

For use with insulated ring terminals and connectors



## Features

Model No.	AS 4054.140
Design	Angled
Product description	For use with insulated ring terminals and connectors.
Benefits	Clear allocation of cross-sections, thanks to colour coding on the dies Releasable ratchet Releases as soon as the required pressure is reached, to prevent underpressing
Material	High-quality special tool steel
Surface finish	Matt, plated
Colour	Handle: Anthracite and Rittal Power Pink
Compression	Oval crimp
Dimensions	Height: 59 mm Length: 198 mm
AWG	22 - 14
For cross-section	0.75 - 2.5 mm <sup>2</sup>
Packs of	1 pc(s).
Weight/pack	0.42 kg
Net weight	0.42

# Features

---

Gross weight	0.44
Customs tariff number	82032000
EAN	4028177807686
ETIM 8	EC000168
ETIM 7.0	EC000168
ECLASS 8.0	21043811

---