

**Rittal – The System.**

Faster – better – everywhere.



**AS 4055.085**

**Manual hydraulic punch set, PG 9 -  
PG 48**

State: 07/10/2024 (Source: [rittal.com/com-en](http://rittal.com/com-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4055.085 - Manual hydraulic punch set, PG 9 - PG 48

Manual hydraulic punch in a practical set with hole punches

## Features

Model No.	AS 4055.085
Design	With 90° angled and 360° rotating cylinder head
Product description	Manual hydraulic punch in a practical set with hole punches for sheet steel. Maximum machinable material thickness 2 or 3 mm.
Benefits	Extend tool life with a built-in overpressure valve
Supply includes	Manual hydraulic punch 9 splitter hole punches, triple splitting Hydraulic screw Ø 19 mm Hydraulic screw Ø 9.5 / 19 mm HSS pilot drill Ø 10 mm Spacer sleeve set (3-part) Plastic case
Maximum machinable material thickness, sheet steel	2 mm 2 mm 2 mm 2 mm 2 mm 3 mm 3 mm 3 mm 3 mm
Ø punch	15.2 mm 18.6 mm 20.4 mm 22.5 mm 28.3 mm 37 mm 47 mm 54 mm 60 mm
Packs of	1 pc(s).

# Features

---

Weight/pack	5.85 kg
Net weight	5.85
Gross weight	5.951
Customs tariff number	84678900
EAN	4028177807969
ETIM 8	EC001085
ETIM 7.0	EC001085
ECLASS 8.0	21049046