

**Rittal – The System.**

Faster – better – everywhere.



# AS 4055.122

## Splitter hole punch, round

State: 07/10/2024 (Source: [rittal.com/com-en](http://rittal.com/com-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4055.122 - Splitter hole punch, round for stainless steel, round, with triple splitting

For punching round cut-outs

## Features

Model No.	AS 4055.122
Design	With triple splitting
Product description	For punching round cut-outs. The hole punch is operated with a wrench or hydraulic punch.
Supply includes	Female dies Male dies
Maximum machinable material thickness, stainless steel	2 mm
Ø punch	22.5 mm
Note	When operating with wrenches, tension screws with ball bearings should be used.
Suitable for hydraulic bolt order number	4055.665
Tension screw (Ø x L)	11.1 x 60 mm
Hydraulic tension screw Ø	11.1 mm 19 cm
Packs of	1 pc(s).
Weight/pack	0.093 kg
Net weight	0.093
Gross weight	0.113
Customs tariff number	82073010
EAN	4028177808010
ETIM 8	EC000156

# Features

---

ETIM 7.0	EC000156
----------	----------

---

ECLASS 8.0	21049047
------------	----------