

Rittal – The System.

Faster – better – everywhere.



PS 4157.000

U nut

State: 12/12/2024 (Source: rittal.com/com-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



PS 4157.000 - U nut

For mounting punched rails and punched sections without mounting flanges on angle brackets, mounting brackets and support brackets.



Features

Model No.	PS 4157.000
Installation options	Punched rail 23 x 23 mm Punched section without mounting flange, 23 x 73 mm Punched section without mounting flange, 45 x 88 mm Punched section with mounting flange, 23 x 73 mm
Note	For mounting punched rails and punched sections without mounting flanges on angle brackets, mounting brackets and support brackets, we recommend U nuts with M6 thread
Dimensions	Thread: M5
Thread	M5
Packs of	20 pc(s).
Net weight	0.34
Gross weight	0.36
Customs tariff number	73181900
EAN	4028177092822
ETIM 9	EC000096
ETIM 8	EC000096
ECLASS 8.0	23110804