



Rittal – The System.

Faster – better – everywhere.



DK 7072.200

Brush strip

State: 23/01/2025 (Source: rittal.com/com-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7072.200 - Brush strip

Cut-outs for cable routing at any given positions in the side panel, rear panel, doors, roof and gland plate may be finished off attractively by simply attaching the brush strip.

Features

| | |
|--------------------------|---|
| Model No. | DK 7072.200 |
| Product description | For individual installation of enclosure panels, gland plates and panels. Cut-outs for cable routing at any given positions in the side panel, rear panel, doors, roof and base plate may be finished off attractively by simply attaching the brush strip. |
| Benefits | Snap-on surface: 10 mm |
| Function principle | Maximum cut-out height: 38 mm |
| Material | Plastic sheathing: 18 mm Brush strip: Plastic, UL 94-HB |
| Bristle length | 30 mm |
| Length | 2 m |
| Dimensions | Length: 2 m |
| For material thicknesses | 0.6 - 1.5 mm |
| Packs of | 1 pc(s). |
| Net weight | 0.43 |
| Gross weight | 0.433 |
| Customs tariff number | 96035000 |
| EAN | 4028177221642 |
| ETIM 9 | EC012298 |
| ECLASS 8.0 | 27142421 |

Tender text

Brush strip

Brush strip, L: 2000 mm,
for sheet thickness: 0.6-1.5 mm

Bristle length: 30 mm

Plastic jacket: 18 mm

Attachable area: 10 mm

Maximum cut-out height: 38 mm