


# Rittal – The System.

Faster – better – everywhere.



## DK 7824.086 Side panel, lockable

State: 26/09/2024 (Source: [rittal.com/com-en](http://rittal.com/com-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7824.086 - Side panel, lockable for TS, TS IT

Side panel, lockable, sheet steel, for TS.

## Features

|                       |   |
|-----------------------|---|
| Model No.             | DK 7824.086   |
| Product description   | Simply locate from above. Lock with security lock no. 3524 E. Earthing bolt with contact track. |
| Material              | Sheet steel   |
| Surface finish        | Spray-finished  |
| Colour                | RAL 7035  |
| Supply includes       | 2 side panels each with 4 security locks no. 3524 E   |
| To fit                | Enclosure type: TS<br>TS IT<br>Height: 800 mm<br>Depth: 600 mm                                  |
| Basic material        | Sheet steel   |
| Packs of              | 2 pc(s).  |
| Weight/pack           | 13.7 kg   |
| Net weight            | 11.4  |
| Gross weight          | 12.4  |
| Customs tariff number | 94039910  |
| EAN                   | 4028177232303   |
| ETIM 7.0              | EC002524  |
| ECLASS 8.0            | 27182101  |

# Tender text

Side panel, plug-type for DK-TS

Lockable side panel with 2 options:

Lockable by exchanging the lock for cam locks with security inserts no. 3524 E.

Additional security is achieved via the option of securing the side panel from inside. The side panels on the frame section are screw-fastened from the inside with securing brackets. The side panel can only be opened in case of access via the front door.

The security standard corresponds to that of the semi-cylinder fitted in the front door.

Plug-and-play attachment via simple plugging-in, closing and locking. The 25 mm pitch pattern of holes integrated within the vertical top hat rail offers additional attachment options for installation or cable routing components.

Material: 1.5 mm sheet steel

Surface finish: RAL 7035

For enclosure dimensions: H: 800 mm D: 600