

Rittal – The System.

Faster – better – everywhere.



DK 7825.360

Gland plate modules, vented

State: 21/02/2025 (Source: rittal.com/com-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7825.360 - Gland plate modules, vented for TS IT, TS, SE, TX CableNet

Gland plate modules, vented, for TS, TS IT, SE for use in the base frame of the network enclosure. Used in exchange for an existing gland plate of the same depth.

Features

Model No.	DK 7825.360
Product description	Large perforated section for passive enclosure ventilation.
Material	Sheet steel
Surface finish	Zinc-plated
Supply includes	Filter mat and nylon tape
Note	Several gland module plates need to be combined to close off the base completely in the TS-IT
Dimensions	Depth: 237.5 mm
To fit	Enclosure type: TS TS IT SE TX CableNet Width: 600 mm
Packs of	1 pc(s).
Net weight	1.27
Gross weight	1.6
Customs tariff number	73269098
EAN	4028177234314
ETIM 9	EC002620
ECLASS 8.0	27189261

Tender text

DK Gland plate module, vented
For cable entry with brush
For W: 600 mm,
Depth: 237,5 mm
For TS, TS IT, SE, TX CableNet
Module plate: Sheet steel
Brush strip: UL 94-HB, halogen-free