

Rittal – The System.

Faster – better – everywhere.



TS 8614.675 Partial mounting plates

State: 27/09/2024 (Source: rittal.com/com-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 8614.675 - Partial mounting plates for TS, VX SE

For universal interior installation and additional mounting levels.



Features

| | |
|---------------------|--|
| Model No. | TS 8614.675 |
| Product description | For universal interior installation, also in conjunction with punched sections with mounting flanges and support strips. Defective assemblies are quickly and easily replaced. Additional mounting levels. |
| Material | Sheet steel, 2.5 mm |
| Surface finish | Zinc-plated |
| Supply includes | Assembly parts |
| Note | Partial mounting plates are fastened directly onto the vertical enclosure sections via the inner mounting level using the assembly parts supplied loose. In this mounting position (in both the width and the depth) they form one level with TS punched sections with mounting flanges 17 x 73 mm and TS support strips for the inner mounting level. |
| Note on Model No. | Also suitable for installing in PC enclosures based on TS behind the lower front door, IW enclosures, height 900 and 1000 mm |

Features

| | |
|-----------------------|---|
| Dimensions | Width: 500 mm Height: 775 mm |
| To fit | Enclosure type: TS VX SE Width: = 600 mm Depth: = 600 mm |
| Packs of | 1 pc(s). |
| Weight/pack | 9.8 kg |
| Net weight | 9.5 |
| Gross weight | 9.76 |
| Customs tariff number | 94039910 |
| EAN | 4028177367890 |
| ETIM 7.0 | EC000213 |
| ECLASS 8.0 | 27409216 |