


Rittal – The System.

Faster – better – everywhere.



SV 9677.958

Current transformer

State: 27/09/2024 (Source: [rittal.com/com-en](https://www.rittal.com/com-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9677.958 - Current transformer

For inductive measurement of current flow.

Features

Model No.	SV 9677.958
Product description	Compact design without altering the installation depth via mechanical integration into the top-mounting components (185 mm centre-to-centre spacing); this allows space-saving assembly.
Material	Polyamide
To fit Model No.	9677930
Rated power input	2.5 VA
Type of electrical connection	Box terminal
Insulation material (class)	H
Primary current	800 A
Secondary current	5 A
Accuracy Class	1
Test specification	IEC 60 044-1 EN 60715 DIN VDE 0414 DIN 42 600-2
Connection for round conductor cross-sections	2.5 - 4 mm ²
Rated frequency	50 - 60 Hz
To fit	9,677,930
Packs of	1 pc(s).
Net weight	0.16
Gross weight	0.17
Customs tariff number	85043129

Features

EAN	4028177984424
ETIM 7.0	EC000001
ECLASS 8.0	27141146