

Rittal – The System.

Faster – better – everywhere.



SZ 2562.100

Metal gland plate

State: 27.09.2024. (Source: [rittal.com/hr-hr](https://www.rittal.com/hr-hr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES



FRIEDHELM LOH GROUP

SZ 2562.100 - Metal gland plate with metric knockouts

Simply knock out the holes for the cable glands using a screwdriver, IP 66 when mounting in the usual position at the bottom.

Features

Model No.	SZ 2562.100
Product description	Simply knock out the holes for the cable glands using a screwdriver.
Material	Sheet steel
Colour	RAL 7035
Note	The allocation of gland plate sizes is indicated on the relevant enclosures
No. of metric knockouts	2 x M16 5 x M20 13 x M25 2 x M32 2 x M40
Dimensions	Width: 339 mm Depth: 149 mm
To fit	Enclosure type: AE
Gland plate	Size: 4
Protection category to IEC 60 529	IP 66 when mounting in the usual position at the bottom
Number knockouts	2 5 13 2 2
Metric diameter	M16 M20 M25 M32 M40
Packs of	1 pc(s).

Features

Weight/pack	0,6 kg
Net weight	0.5
Gross weight	0.62
Customs tariff number	73269098
EAN	4028177390867
E-Number Sweden	E3404796
ETIM 8	EC000211
ETIM 7.0	EC000211
ECLASS 8.0	27142421