

**Rittal – The System.**

Faster – better – everywhere.



# SK 3171.100

## Chopped-fibre filter mat

State: 27.09.2024. (Source: [rittal.com/hr-hr](https://www.rittal.com/hr-hr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3171.100 - Chopped-fibre filter mat

Spare filter mats for roof-mounted fans, fan-and-filter units or thermoelectric coolers, for effective protection of enclosure components from dirt, dust and water.

## Features

Model No.	SK 3171.100
Design	for fan-and-filter units
Product description	Made of chopped-fibre mat with a progressive structure. Temperature-resistant to 100 °C, self-extinguishing category F1 to DIN 53 438. Dust-laden air side: Open structure. Clean-air side: Closed structure. Reliable filtering of virtually all types of dust from a particle size of 10 µm.
Material	Chemical fibres
Note	No suitable for use in EMC fan-and-filter units.
To fit Model No.	3239....
Dimensions	Width: 173 mm Height: 173 mm Depth: 17 mm
Filter class	to DIN EN 779: G3 to DIN EN ISO 16890: ISO Coarse 50%
Weight/pack	0,05 kg
Packs of	5 pc(s).
Net weight	0.045
Gross weight	0.25
Customs tariff number	56039390
EAN	4028177038059
E-Number Sweden	E3404740
ETIM 8	EC002513
ETIM 7.0	EC002513

# Features

---

ECLASS 8.0

27180706

# Approvals

---

Approvals

UR + C-UR (recognized)

Certificates

EAC