

**Rittal – The System.**

Faster – better – everywhere.



# DK 7016.140

## Cable clamp, variable

State: 27.09.2024. (Source: [rittal.com/hr-hr](https://www.rittal.com/hr-hr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7016.140 - Cable clamp, variable for enclosure-independent mounting

For enclosure-independent mounting, variable attachment from 450 to 800 mm for flexible cable clamping in two variants: as C rails or T-head rail.

## Features

Model No.	DK 7016.140
Design	C rail
Product description	Variable attachment from 450 to 800 mm for flexible cable clamping in two variants. Supports attachment to punched sections with and without mounting flanges and direct screw-fastening onto mounting plates and other panels.
Material	Sheet steel
Surface finish	Zinc-plated
Supply includes	Assembly parts
Packs of	1 pc(s).
Weight/pack	0,92 kg
Net weight	0.81
Gross weight	0.9
Customs tariff number	73269098
EAN	4028177550384
ETIM 7.0	EC002620
ECLASS 8.0	27189261

# Tender text

Cable clamping, variable, C-rail version

Cable clamp rail, length-adjustable, for flexible attachment irrespective of the enclosure system used.

Variable attachment of 450 - 800 mm.

The cable clamping takes place by means of fixing with cable clamps in the C-section.

Dimensions: L(mm): 450 - 800 mm

Sheet steel, zinc-plated, passivated