

Rittal – The System.

Faster – better – everywhere.



DK 7246.400 Adaptor, 3 U

State: 27.09.2024. (Source: rittal.com/hr-hr)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7246.400 - Adaptor, 3 U Depth offset 100 mm

Used to recess 482.6 mm (19") mounting of equipment inside enclosures with 482.6 mm (19") installation in the foremost position, such as server or electronic enclosures.



Features

Model No.	DK 7246.400
Product description	This adaptor is used to recess 482.6 mm (19") mounting of equipment inside enclosures with 482.6 mm (19") installation in the foremost position, such as server or electronic enclosures. In this way, sufficient space can be gained in front of the mounting equipment to integrate patch panels or switches, whilst at the same time exploiting the maximum enclosure depth.
Material	Sheet steel
Surface finish	Zinc-plated
Supply includes	Assembly parts
Units	3 U
Installation dimensions	Installation depth for components: 482.6 mm Installation width for components: 19"
Packs of	2 pc(s).
Weight/pack	0,36 kg
Net weight	0.34
Gross weight	0.37
PCF/PU (Cradle-to-Gate)	1.4 kg CO2 eq (Cat B)

Features

Note on the PCF class	Category B: PCF value (cradle-to-gate) approximated based on product weight and self-declared
Customs tariff number	73269098
EAN	4028177389830
ETIM 7.0	EC002625
ECLASS 8.0	27189234

Tender text

482.6 mm (19") adaptor, 3 U, 100 mm depth offset
Material: Sheet steel, zinc-plated, passivated