

# Rittal – The System.

Faster – better – everywhere.



## DK 7831.463 Colocation racks TS

State: 27.09.2024. (Source: [rittal.com/hr-hr](http://rittal.com/hr-hr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7831.463 - Colocation racks TS

Colocation rack TS 8 with 2/4 separate functional areas.

## Features

Model No.	DK 7831.463
Benefits	Robust frame structure Front and rear door vented across the entire surface Open surface area > 78 % perforated 2-point locking Door hinge may be swapped to opposite side without machining Cable entry via the base/plinth and roof (optional) Bayable at all levels Static load capacity of up to 1000 kg
Material	Sheet steel
Surface finish	Enclosure frame: Dipcoat-primed Enclosure panels: Dipcoat-primed, powder-coated Mounting angles, mounting frame and punched sections with mounting flanges: Zinc-plated, passivated
Colour	RAL 7035
Supply includes	Sheet steel doors, vented, front and rear with 180° hinges Roof plate, one-piece, solid Levelling feet 482.6 mm (19") level, L-shaped mounting angles on punched sections with mounting flanges, front and rear, depth-variable Earthing of all enclosure panels pre-configured Individual compartments, shielded/separate cable routing per compartment Comfort handle for profile half-cylinders with security lock 3524 E
Dimensions	Width: 600 mm Height: 2,200 mm Depth: 1,000 mm
Installation height for components per door	10 U

# Features

Distance between levels as delivered	740 mm
Number front doors	4
Number back doors	4
Note on Model No.	Extended delivery times.
Basic material	Sheet steel
Packs of	1 pc(s).
Weight/pack	154 kg
Net weight	148
Gross weight	154
EAN	4028177642737
ETIM 7.0	EC002499
ECLASS 8.0	27180207