

Rittal – The System.

Faster – better – everywhere.



VX 8618.000 Glazed door

State: 19.10.2024. (Source: [rittal.com/hr-hr](https://www.rittal.com/hr-hr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 8618.000 - Glazed door for VX

Instead of a sheet steel door or rear panel.

Features

| | |
|-------------------------------------|---|
| Model No. | VX 8618.000 |
| Product description | Instead of a sheet steel door or rear panel. |
| Material | Frame: Extruded aluminium section Viewing window: Single-pane safety glass, 3 mm |
| Surface finish | Powder-coated |
| Colour | Frame: RAL 7035 Viewing window (printed mask on the inside): RAL 9005 |
| Supply includes | Glazed door Locking rod with double-bit insert 180° hinges (4) |
| IK Code | IK08 |
| Note | Lock components for frame 8618.110 are required when mounting instead of the rear panel |
| Type rating to UL 50E | Type 1 Type 12 |
| IP protection category to IEC 60529 | IP 55 |
| To fit | Enclosure type: VX Width: = 600 mm Height: = 1,800 mm |
| Packs of | 1 pc(s). |
| Weight/pack | 13 kg |
| Net weight | 12.4 |
| Gross weight | 13 |
| EAN | 4028177921085 |
| ETIM 7.0 | EC000747 |

Features

ECLASS 8.0

27182204

Approvals

Approvals

UL + C-UL - FTTA

Certificates

Protection category