

Rittal – The System.

Faster – better – everywhere.



SV 9342.324

Connection adaptor expansion set

State: 26.09.2024. (Source: rittal.com/hr-hr)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9342.324 - Connection adaptor expansion set for 4-pole configuration

Single-pole extra set to complement the 3-pole connection adaptor (SV 9342.310/9342.320) for 4-pole configurations.

Features

Model No.	SV 9342.324
Product description	Single-pole extra set to complement the 3-pole connection adaptor for 4-pole configurations.
Material	Cover: ABS Punched section: Polyamide Fire protection corresponding to UL 94-V0
Colour	RAL 7035
Rated current max.	1.600 A
Rated operating voltage	690 V, 1~
Electrical ratings UL (SCCR)	65 kA - 480 V, circuit breaker max. 1200 A, DIVQ/7 65 kA - 600 V, Fuse Class L max. 1600 A, JDDZ/7
For bar systems with centre-to-centre spacing	60 mm
Note	The technical data may vary for UL applications UL approval only applies in conjunction with AC application
Number of poles	Single-pole
To fit Model No.	9342.320
Dimensions	Width: 85 mm Height: 270 mm
To fit busbars	Height: 5, 10 mm
Clamping area for laminated copper bars with 5 mm bar thickness (W x H)	65 x 27 mm

Features

Clamping area for laminated copper bars with 10 mm bar thickness (W x H)	65 x 22 mm
--	------------

Packs of	1 pc(s).
----------	----------

Weight/pack	1,3 kg
-------------	--------

Net weight	0.199
------------	-------

Gross weight	1.271
--------------	-------

Copper weight (kg per piece)	0.136
------------------------------	-------

Customs tariff number	85369010
-----------------------	----------

EAN	4028177536876
-----	---------------

ETIM 7.0	EC001531
----------	----------

ECLASS 8.0	27370304
------------	----------

Approvals

Approvals	ABS C-UL DNV-GL Lloyds Register of Shipping UL + C-UL (listed)
-----------	--

Explanations	Declaration of conformity Declaration of conformity UK
--------------	---