

Rittal – The System.

Faster – better – everywhere.



CP 6206.480

Connection console VESA 75/100

State: 2024.9.26 (Source: rittal.com/lt-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CP 6206.480 - Connection console VESA 75/100

For rear connection of flat command panels, standard TFTs and industrial PCs with VESA 75/100 connection. May be connected to Rittal support arm systems CP 40 and CP 60, and also CP 120 by using an adaptor from support arm connection Ø 130 mm to rectangular 120 x 65 mm.



Features

| | |
|---------------------|---|
| Model No. | CP 6206.480 |
| Design | Connection to Rittal support arm systems |
| Product description | For rear connection of flat command panels, standard TFTs and industrial PCs with VESA 75 / 100 connection. |
| Benefits | Fast, simple one-man assembly using machined keyholes More space for installation and servicing Cables may be routed to devices outside and below the console Removable cover for simple cable routing and access to interior device connections Integral cable clamping facilities Cover and captive screws |
| Material | Die-cast zinc |
| Colour | Connection console: RAL 7035 Cover: RAL 7024 |
| Supply includes | Seal and assembly parts Cable ties for cable clamping |
| Rifid y/n | Yes |
| Note | Depending on the application, an attachment, coupling or adaptor are required |
| Load capacity | 800 N |

Features

| | |
|-----------------------|---------------|
| Packs of | 1 pc(s). |
| Weight/pack | 1.1 kg |
| Net weight | 2.5 |
| Gross weight | 2.775 |
| Customs tariff number | 79070000 |
| EAN | 4028177693920 |
| ETIM 7.0 | EC002622 |
| ECLASS 8.0 | 27189263 |

Approvals

| | |
|--------------|----------------------------|
| Explanations | Manufacturer's declaration |
|--------------|----------------------------|