

Rittal – The System.

Faster – better – everywhere.



CP 6315.200

Command panels with handle strips

State: 2024.10.19 (Source: [rittal.com/lt-en](https://www.rittal.com/lt-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CP 6315.200 - Command panels with handle strips

Operating housings with modern sheet steel handle strips, with support arm cut-out Ø 130 mm to fit support arm system CP 60 / 120 / 180, service access optionally from the front or rear, aluminium front panel easily removable for machining, protection category IP 55.



Features

| | |
|-----------------|---|
| Model No. | CP 6315.200 |
| Material | Enclosure and door: Sheet steel Handle strips: Aluminium Front panel: Aluminium Cover caps: Plastic |
| Surface finish | Enclosure and door: Dipcoat primed, powder-coated on the outside, textured paint Handle strip: Natural anodised Front panel: Natural anodised |
| Colour | Enclosure and door: RAL 7035 Handle strip: Natural anodised Front panel: Natural anodised Cover caps: similar to RAL 7024 |
| Supply includes | Enclosure with cut-out and reinforcement for support arm connection Ø 130 mm Front with maximum cut-out, covered with easily machinable 3 mm aluminium front panel Side handle strips and cover caps Cam lock with 3 mm double-bit insert Integral interior installation bracket with TS system punchings |

Features

| | |
|-------------------------------------|---|
| Dimensions | Width: 380 mm Height: 300 mm Depth: 210 mm |
| IP protection category to IEC 60529 | IP 55 |
| Design | Servicing access from the front |
| Note | The support arm connection and door hinge may be swapped over by rotating the enclosure Optional: Support arm connection Ø 130 mm, preformed off-centre in the reinforcement plate, easily drilled out Lock systems for servicing access from the front: 41 mm lock inserts, type C, lock cylinder, plastic handles and T handles, type C |
| Basic material | Aluminium |
| Note on Model No. | Matching mounting panel 5050.430 with dispatch bag 5050.507 |
| Lock | Lock version: Crescent-shaped cam Number of locks: 1 Lock insert: 3 mm double-bit |
| Packs of | 1 pc(s). |
| Weight/pack | 7.5 kg |
| Net weight | 7.955 |
| Gross weight | 8.374 |
| Customs tariff number | 94032080 |
| EAN | 4028177693944 |
| ETIM 7.0 | EC002504 |
| ECLASS 8.0 | 27180505 |

Approvals

| | |
|--------------|---------------------------|
| Approvals | Bureau Veritas |
| Explanations | Declaration of conformity |