

Rittal – The System.

Faster – better – everywhere.



CP 6514.200

Utility bar, vertically hinged

State: 2024.9.26 (Source: [rittal.com/lt-en](https://www.rittal.com/lt-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CP 6514.200 - Utility bar, vertically hinged

To support standard keyboards during programming and servicing work. Mounting distance between utility bars at least 300 mm to allow problem-free insertion.



Features

Model No.	CP 6514.200
Product description	To support standard keyboards during programming and servicing work. Mounting distance of utility bars for problem-free insertion at least 300 mm. Depth adequate for keyboards up to max. 210 mm.
Benefits	After use, the utility bars fit securely and neatly under the mounting surface, thus giving the operator more space to move around.
Material	Sheet steel
Surface finish	Zinc-plated
Supply includes	Assembly parts
Installation options	under Comfort Panels (min. front panel width 385 mm) under Optipanel (min. front panel width 405 mm) Underneath sufficiently large surfaces such as IW worktops, AX command panels with handle strips on vertical surfaces (doors/side panels)
Packs of	2 pc(s).
Weight/pack	1.09 kg
Net weight	1
Gross weight	1.089
PCF/PU (Cradle-to-Gate)	4.2 kg CO2 eq (Cat B)

Features

Note on the PCF class	Category B: PCF value (cradle-to-gate) approximated based on product weight and self-declared
Customs tariff number	73269098
EAN	4028177388260
ETIM 7.0	EC002620
ECLASS 8.0	27189261