

# Rittal – The System.

Faster – better – everywhere.



## DK 7501.000 VerticalBox

State: 2024.9.27 (Source: [rittal.com/lt-en](http://rittal.com/lt-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7501.000 - VerticalBox

Compact 482.6 mm (19") enclosure for small networks that may be used as a wall-mounted, under-desk or desktop enclosure.

## Features

Model No.	DK 7501.000
Product description	Compact 482.6 mm (19") enclosure for small networks.
Benefits	May be used as wall-mounted, under-desk or desktop enclosure Free access from three sides for interior installation Passive ventilation with vent slots Rear panel prepared to accommodate a fan Freely selectable door hinging Space-saving, vertical mounting of 482.6 mm (19") installation components at the side
Material	Sheet steel Viewing window: Single-pane safety glass, 3 mm
Surface finish	Powder-coated
Colour	RAL 7035
Supply includes	Enclosure with glazed door Side panels (1 x fixed, 1 x slot-in) with vent slots Knockouts for cable entry via roof or base Slot-in rear panel with knockouts for cable entry and fan accommodation 482.6 mm (19") mounting level, 5 U, horizontal front and rear, depth-variable, distance between levels 434 – 489 mm Security lock 12321 on the door, side and rear panel 4 plastic feet, self-adhesive
Units	5 U
Dimensions	Width: 300 mm Height: 540 mm Depth: 600 mm
Installation height for components	5 U
Basic material	Sheet steel

## Features

---

Load capacity	250 N
Max. load capacity (static) per enclosure to UL 2416	250 N
Packs of	1 pc(s).
Weight/pack	17.04 kg
Net weight	16.188
Gross weight	17.04
PCF/PU (Cradle-to-Gate)	64.9 kg CO2 eq (Cat B)
Note on the PCF class	Category B: PCF value (cradle-to-gate) approximated based on product weight and self-declared
Customs tariff number	94032080
EAN	4028177625426
ETIM 7.0	EC002500
ECLASS 8.0	27180208

## Approvals

---

Explanations	Manufacturer's declaration
--------------	----------------------------

# Tender text

Compact 482.6 mm (19 inch) enclosure for small networks

May be used as a wall-mounted, under-desk or desktop enclosure, depending on requirements.

Supply includes:

482.6 mm (19") enclosure, 5 U, with a mounting level front and rear.

Glazed front door, one side panel fixed, one plug-in, removable, plug-in rear panel, removable, with opening for cable entry, prepared to accommodate one fan unit.

Glazed door, side panel and rear panel with security lock 12321.

Roof and base with vent slots and knock-outs for cable entry.

4 plastic feet, self-adhesive, supplied loose.

Material: Sheet steel, viewing window toughened safety glass, 3 mm

Colour: RAL 7035