

# Rittal – The System.

Faster – better – everywhere.



## DK 7502.124

## QuickBox, 482.6 mm (19")

State: 26/09/2024 (Source: [rittal.com/nz-en](http://rittal.com/nz-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7502.124 - QuickBox, 482.6 mm (19")

Wall-mounted enclosure with removable cover for simple installation and horizontal 482.6 mm (19") level. Status monitoring via viewing window.

## Features

Model No.	DK 7502.124
Design	With sheet steel door
Product description	Wall-mounted enclosure with removable cover for perfect handling during installation and maintenance.
Material	Wall mounting plate with mounting brackets: Sheet steel, 2.0 mm Enclosure cover: Sheet steel, 1.0 mm Door: Sheet steel door or glazed door with sheet steel frame and single-pane safety glass, 3 mm
Surface finish	Enclosure: Powder-coated
Colour	RAL 7035
Supply includes	Wall section: with pre-configured mounting brackets, brush strip for cable entry at the bottom/top, cable clamp rail, 482.6 mm (19") mounting angles, fully depth adjustable Enclosure cover: Base and cover tray with vent slots, brush strip for cable entry at the top/bottom, 2 side security locks, sheet steel door or glazed door with security lock 12321, version with Ergoform-S lock system, may optionally be retrofitted with semi-cylinder.
Units	9 U
Dimensions	Width: 600 mm Height: 495 mm Depth: 400 mm
Installation depth	347 mm
Depth of wall section	488 mm
Width wall section	595 mm
Basic material	Sheet steel
Packs of	1 pc(s).

# Features

---

Weight/pack	22.4 kg
Net weight	21.28
Gross weight	22.4
Customs tariff number	94032080
EAN	4028177201361
E-Number Sweden	E7239624
ETIM 7.0	EC002500
ECLASS 8.0	27180208

# Tender text

Wall-mounted enclosure with 482.6 mm (19 inch) level

## Enclosure:

9 U wall-mounted enclosure consisting of wall section and enclosure cover with front door.

Wall section: Wall mounting plate with pre-configured mounting brackets on the left and right hand side, mounting brackets for the attachment of imperial or metric mounting angles and for accommodation of cable routing accessories with cutouts for cable entry.

A set of 482.6 mm (19 inch) mounting angles screw-fastened to mounting brackets, infinitely depth-variable. A 400 mm wide T-head rail for cable clamping with cable ties, mounted on the wall-section. Four holes for direct wall-mounting or by means of optional wall mounting brackets.

Enclosure cover with side vent slots for passive ventilation, with security locks on the left and right hand side. Apertures for cable entry in the rear section at top and bottom, covered with brush inserts.

Front door, one-part, solid, with security lock no. 12321

## Material:

Wall section, enclosure cover, front door of sheet steel

## Surface finish

Electrophoretic-dipcoat primed, spray-finished in RAL 7035

## Dimensions (W x H X D)

600 x 495 x 400 mm / (9 U)