


# Rittal – The System.

Faster – better – everywhere.



## SV 3055.000

## Suporte de barramento

Estado: 26-09-2024 (Fonte: [rittal.com/pt-pt](http://rittal.com/pt-pt))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 3055.000 - Suporte de barramento

Para sistemas de barramento 1250 A (100 mm), 1600 A (185 mm), 2500 A (150 mm), 3000 A (150 mm).



## Recursos

Cód. Ref.	SV 3055.000
Material	Poliéster termoplástico (PBT) reforçado com fibra de vidro Proteção contra incêndio segundo a norma UL 94-V0
Cor	RAL 7035
Qtd. de polos	3 polos 150 mm
Adequado para barras	60 x 10 80 x 10
Corrente nominal máx.	2500 A
Dimensões	Largura: 30 mm Altura: 420 mm Profundidade: 160 mm
Emb.	2 unid.
Peso/embalagem	4,54 kg
Peso líquido	4.16
Peso bruto	4.503
Número da tarifa alfandegária	85469010
EAN	4028177035782

## Recursos

---

ETIM 8	EC001166
ETIM 7.0	EC001166
ECLASS 8.0	27400607

---

## Aprovações

---

Explicações	Declaration of conformity Declaración de conformidad UK
-------------	--