

Rittal – The System.

Faster – better – everywhere.



KL 1527.010

Kopplingslådor KL

State: 2024-09-27 (Source: [rittal.com/se-sv](https://www.rittal.com/se-sv))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



KL 1527.010 - Kopplingslådor KL Rostfritt stål

Kopplingslåda av rostfritt stål 1.4301 (AISI 304). Kapslingsklass IP 66.

Features

Art. nr.	KL 1527.010
Material	Skåp: Rostfritt stål 1,4301 (AISI 304) Lock: Rostfritt stål 1.4301 (AISI 304), omgivande inskummad PU-tätning
Ytbehandling	Skåp och lock: Streckslipat, korn 180
Leveransens omfattning	Skåp med lock Snabbkoppling inkl. plasthylsor
Protection category NEMA	NEMA 4X
Kapslingsklass IP enligt EN 60 529	IP 66
IK-kod	IK08
Dimension	Bredd: 150 mm Höjd: 150 mm Djup: 120 mm
Materialtjocklek lock	1,25 mm
Materialtjocklek låda	1,25 mm
Lås	Antal lås: 4
Grundmaterial	Rostfritt stål 1.4301 (AISI 304)
Förpackningsenhet	1 st.
Vikt/förp.	1,6 kg
Nettovikt	1.4
Bruttovikt	1.484
Tullvarukod	84879090
EAN	4028177663329
E-Number Sweden	E3404378

Features

ETIM 8	EC000261
ETIM 7.0	EC000261
ECLASS 8.0	27180101

Approvals

Approvals	Bureau Veritas DNV-GL Lloyds Register of Shipping UL + C-UL (listed)
Explanations	Konformitetsförklaring Konformitetsförklaring UK
