

Rittal – The System.

Faster – better – everywhere.



BG 1585.010 Bus-skåp BG

State: 2024-10-19 (Source: [rittal.com/se-sv](https://www.rittal.com/se-sv))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



BG 1585.010 - Bus-skåp BG Rostfritt stål

Bus-skåp av rostfritt stål 1.4301, (AISI 304), inkl. 180°-gångjärn. Kapslingsklass IP 66.

Features

Art. nr.	BG 1585.010
Material	Skåp: Rostfritt stål 1,4301 (AISI 304) Lock: Rostfritt stål 1.4301 (AISI 304), omgivande inskummad PU-tätning 180°-gångjärn: zinkjutgods
Ytbehandling	Skåp och lock: Streckslipat, korn 240 180°-gångjärn: kromade
Leveransens omfattning	Skåp med lock 180°-gångjärn (2 stycken) Profilskena TH 35/7,5 Snabbkoppling inkl. plasthylsor
Protection category NEMA	NEMA 4X
Kapslingsklass IP enligt EN 60 529	IP 66
Dimension	Bredd: 400 mm Höjd: 300 mm Djup: 80 mm
Materialtjocklek låda	1,5 mm
Materialtjocklek dörr	1,25 mm
Position dörrupphängning	höger/vänster
Antal profilskenor	1
Lås	Utförande för lås: Snabbkoppling inkl. plasthylsor Antal lås: 2
Grundmaterial	Rostfritt stål 1.4301 (AISI 304)
Förpackningsenhet	1 st.
Vikt/förp.	4,5 kg
Nettovikt	3.55

Features

Bruttovikt	4.16
Tullvarukod	94032080
EAN	4028177011014
ETIM 8	EC000261
ETIM 7.0	EC000261
ECLASS 8.0	27180101

Approvals

Approvals	Lloyds Register of Shipping UL + C-UL (listed)
Explanations	Konformitetsförklaring Konformitetsförklaring UK