

Rittal – The System.

Faster – better – everywhere.



AX 2574.100

Plåtfläns i metall

State: 2025-04-08 (Source: [rittal.com/se-sv](https://www.rittal.com/se-sv))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AX 2574.100 - Plåtfläns i metall med metrisk förprägling, för AX

Hål för kabelförskruvningar slås lätt ut med en skruvmejsel.

Features

| | |
|------------------------------------|---|
| Art. nr. | AX 2574.100 |
| Produktbeskrivning | Hål för kabelförskruvningar slås lätt ut med en skruvmejsel. |
| Material | Stålplåt |
| Färg | RAL 7035 |
| Observera: | Tilldelningen av flänsarnas storlek anges vid respektive låda |
| Antal metriska förpräglingar | 1 x M12 6 x M16 8 x M20 11 x M25 6 x M32 4 x M40 |
| Dimension | Bredd: 534 mm Djup: 149 mm |
| Passar för | Skåptyp: AX |
| Plåtfläns | Storlek: 4 |
| Kapslingsklass IP enligt EN 60 529 | IP 66 vid korrekt montage |
| Typklassning motsvarande UL 50E | Typ 1 Type 12K |
| Number knockouts | 1 6 8 11 6 4 |

Features

| | |
|-------------------------------|--|
| Metric diameter | M12 M16 M20 M25 M32 M40 |
| Förpackningsenhet | 1 st. |
| Nettovikt | 0.98 |
| Bruttovikt | 0.98 |
| PCF per pack (cradle-to-gate) | 4,9 kg CO2 eq (Cat B) |
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Tullvarukod | 73269098 |
| EAN | 4028177925212 |
| E-Number Sweden | E3465298 |
| ETIM 9 | EC000211 |
| ETIM 8 | EC000211 |
| ECLASS 8.0 | 27142421 |

Approvals

| | |
|-----------|------------------|
| Approvals | UL + C-UL - FTTA |
|-----------|------------------|