

Rittal – The System.

Faster – better – everywhere.



FT 2735.250 System windows

State: 19/10/2024 (Source: rittal.com/sg-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



FT 2735.250 - System windows for VX, TS, VX SE

To conceal display and operating instruments or cut-outs, and to protect against dirt and liquids as well as unauthorised access.

Features

| | |
|-----------------------------------|---|
| Model No. | FT 2735.250 |
| Design | 30 section |
| Product description | To conceal display and operating instruments or cut-outs, and to protect against dirt and liquids as well as unauthorised access. |
| Material | Extruded aluminium section with die-cast zinc corner pieces and single-pane safety glass. |
| Surface finish | Base frame: Powder-coated on the outside in RAL 7035 Hinge and lock section: Natural-anodised |
| Value base frame | Made from single-pane safety glass: High level of resistance to solvents and scratches, anti-static, reduced risk of injury if broken. Standard double-bit lock insert may be exchanged for lock inserts 27 mm, type A, and/or for lock system Ergoform-S (except H = 270 mm). Hinge with 180° opening angle, easily inserted. |
| Value base frame | Easily screw-fastened to the door thanks to modified dimensions (tubular door frame may be used as a drilling template). Readily height-adjustable. Stabilises the door cut-out. Conceals the cut edge. There is no dirt on the seal, the glass is protected from being lifted out, dirt cannot drop inside, and moisture cannot run behind the window when opening. Frame section height 30 mm or 60 mm |
| Protection category to IEC 60 529 | IP 54 |
| Note | Standard double-bit lock insert may be exchanged for lock inserts 27 mm, type A, and/or for lock system Ergoform-S (except H = 270 mm). Not suitable for outdoor siting |

Features

| | |
|-----------------------------------|---|
| To fit | Enclosure type: VX TS VX SE Width: = 800 mm |
| Dimensions | Width: 700 mm Height: 670 mm Depth: 47 mm |
| Visible area | Viewing window width: 563 mm Viewing window height: 598 mm |
| Build depth for components (max.) | 33 mm |
| Packs of | 1 pc(s). |
| Weight/pack | 7.25 kg |
| Net weight | 6.853 |
| Gross weight | 7.214 |
| Customs tariff number | 76101000 |
| EAN | 4028177476370 |
| ETIM 8 | EC002527 |
| ETIM 7.0 | EC002527 |
| ECLASS 8.0 | 27182301 |

Approvals

| | |
|--------------|---------------------|
| Certificates | Protection category |
|--------------|---------------------|