

# Rittal – The System.

Faster – better – everywhere.



## FT 2736.510 System windows

State: 27/09/2024 (Source: [rittal.com/sg-en](http://rittal.com/sg-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# FT 2736.510 - System windows for VX, TS, VX SE

To conceal display and operating instruments or cut-outs, and to protect against dirt and liquids as well as unauthorised access.

## Features

|                                   |   |
|-----------------------------------|---|
| Model No.                         | FT 2736.510   |
| Design                            | 60 section  |
| Product description               | To conceal display and operating instruments or cut-outs, and to protect against dirt and liquids as well as unauthorised access.   |
| Material                          | Extruded aluminium section with die-cast zinc corner pieces and single-pane safety glass.   |
| Surface finish                    | Base frame: Powder-coated on the outside in RAL 7035<br>Hinge and lock section: Natural-anodised  |
| Value base frame                  | Made from single-pane safety glass: High level of resistance to solvents and scratches, anti-static, reduced risk of injury if broken. Standard double-bit lock insert may be exchanged for lock inserts 27 mm, type A, and/or for lock system Ergoform-S (except H = 270 mm).<br>Hinge with 180° opening angle, easily inserted.   |
| Value base frame                  | Easily screw-fastened to the door thanks to modified dimensions (tubular door frame may be used as a drilling template).<br>Readily height-adjustable.<br>Stabilises the door cut-out.<br>Conceals the cut edge.<br>There is no dirt on the seal, the glass is protected from being lifted out, dirt cannot drop inside, and moisture cannot run behind the window when opening.<br>Frame section height 30 mm or 60 mm |
| Protection category to IEC 60 529 | IP 54   |
| Note                              | Standard double-bit lock insert may be exchanged for lock inserts 27 mm, type A, and/or for lock system Ergoform-S (except H = 270 mm).<br>Not suitable for outdoor siting  |

# Features

---

|                                   |   |
|-----------------------------------|---|
| To fit                            | Enclosure type: VX<br>TS<br>VX SE<br>Width: = 600 mm          |
| Dimensions                        | Width: 500 mm<br>Height: 370 mm<br>Depth: 77 mm               |
| Visible area                      | Viewing window width: 363 mm<br>Viewing window height: 298 mm |
| Build depth for components (max.) | 63 mm   |
| Packs of                          | 1 pc(s).  |
| Weight/pack                       | 4.8 kg  |
| Net weight                        | 4.542   |
| Gross weight                      | 4.742   |
| Customs tariff number             | 76101000  |
| EAN                               | 4028177476417   |
| ETIM 8                            | EC002527  |
| ETIM 7.0                          | EC002527  |
| ECLASS 8.0                        | 27182301  |

---

# Approvals

---

|              |                     |
|--------------|---------------------|
| Certificates | Protection category |
|--------------|---------------------|