

# Rittal – The System.

Faster – better – everywhere.



## AS 4054.141 Crimping pliers

State: 19.10.2024 (Source: [rittal.com/si-sl](https://www.rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4054.141 - Crimping pliers for ring terminals

For use with insulated ring terminals and connectors



## Features

Model No.	AS 4054.141
Design	Straight
Product description	For use with insulated ring terminals and connectors.
Benefits	Clear allocation of cross-sections, thanks to colour coding on the dies Releasable ratchet Releases as soon as the required pressure is reached, to prevent underpressing
Material	High-quality special tool steel
Surface finish	Matt, plated
Colour	Handle: Anthracite and Rittal Power Pink
Compression	Oval crimp
Dimensions	Height: 68 mm Length: 256 mm
AWG	22 - 10
For cross-section	0.75 - 6 mm <sup>2</sup>
Packs of	1 pc(s).
Weight/pack	0,64 kg
Net weight	0.64

# Features

---

Gross weight	0.68
Customs tariff number	82032000
EAN	4028177807693
ETIM 8	EC000168
ETIM 7.0	EC000168
ECLASS 8.0	21043811

---