


Rittal – The System.

Faster – better – everywhere.



DK 7824.120 Side panel, lockable

State: 19.10.2024 (Source: [rittal.com/si-sl](https://www.rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7824.120 - Side panel, lockable for TS, TS IT

Side panel, lockable, sheet steel, for TS.



Features

Model No.	DK 7824.120
Product description	Simply locate from above. Lock with security lock no. 3524 E. Earthing bolt with contact track.
Material	Sheet steel
Surface finish	Spray-finished
Colour	RAL 7035
Supply includes	2 side panels each with 4 security locks no. 3524 E
To fit	Enclosure type: TS TS IT Height: 1,200 mm Depth: 1,000 mm
Basic material	Sheet steel
Packs of	2 pc(s).
Weight/pack	29,8 kg
Net weight	28.6
Gross weight	29.8
Customs tariff number	94039910
EAN	4028177330672
E-Number Sweden	E7239565

Features

ETIM 7.0	EC002524
ECLASS 8.0	27182101

Tender text

Side panel, plug-type for TS
H x D = 1200 x 1000 mm, RAL 7035

Side panel fitted with a T-lock.
Material: Sheet steel, spray finished in RAL 7035
For 1200 mm x 1000 mm enclosures