


Rittal – The System.

Faster – better – everywhere.



VX 8619.730

Punched section with mounting flange, 14 x 39 mm

State: 27.9.2024 (Source: [rittal.com/si-sl](https://www.rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 8619.730 - Punched section with mounting flange, 14 x 39 mm for VX, VX SE, PC, IW, AX

For securing cable ducts, cable conduit holders, equipment installed on the door, etc.



Features

Model No.	VX 8619.730
Product description	For attaching cable ducts, cable conduit holders, equipment installed on the door, etc.
Material	Sheet steel
Surface finish	Zinc-plated
Supply includes	Assembly parts
Distance between fixing points	675 mm
To fit door width	800 mm
VX installation options	In door width 800 mm
VX SE installation options	In door width 800 mm
AX installation options	In enclosure height 800 mm, in conjunction with rail for interior installation AX
Installation options, AX plastic	In door width 800 mm
PC installation options	In door width 800 mm
Installation options CX	In door width 800 mm
Assembly instruction	For installation in AX sheet steel, only in conjunction with rail for interior installation AX

Features

Note	For installing your own components on the punched section with mounting flange, metal screws or self-tapping M5 screws are required
To fit	Enclosure type: VX VX SE PC AX AX plastic null CX pedestal Suitable for width or height or depth: 800 mm
To fit	Base/plinth system VX
Packs of	4 pc(s).
Weight/pack	1,6 kg
Net weight	1.4
Gross weight	1.588
Customs tariff number	73269098
EAN	4028177924666
E-Number Sweden	E3465282
ETIM 7.0	EC002625
ECLASS 8.0	27189234