

Rittal – The System.

Faster – better – everywhere.



SV 9346.060 NH slimline fuse-switch disconnecter

State: 26.9.2024 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9346.060 - NH slimline fuse-switch disconnecter



Features

Model No.	SV 9346.060
Material	Fibreglass-reinforced polyamide Fire protection corresponding to UL 94-V0 Contact tracks: Silver-plated hard copper
Colour	Chassis: RAL 7035 Cover: RAL 7001 Handle: RAL 7016
For bar systems with centre-to-centre spacing	100 mm
Cable outlet	Top/bottom
Type of electrical connection	Screw M8
Rated operating current max.	160 A
For NH size	00
Test specification	IEC/DIN EN 60 947-3 DIN EN 60 269-2 (fuse inserts)
For converter installation	Yes
Dimensions	Width: 50 mm Height: 400 mm
Connection for round conductor cross-sections	2.5 - 95 mm ²
To fit busbars	Height: 5, 10 mm

Features

Rated operating voltage	690 V, 3~
Number of poles	3-pole
Packs of	1 pc(s).
Weight/pack	1,18 kg
Net weight	1.179
Gross weight	1.18
Copper weight (kg per piece)	0.65
Customs tariff number	85365080
EAN	4028177668133
ETIM 7.0	EC001046
ECLASS 8.0	27371402

Approvals

Explanations	Declaration of conformity Declaration of conformity UK
--------------	---